

Bellows suction cups (round)

FSGA 22 NK-45 G1/8-IG

Part no.:10.01.06.00413

<https://www.schmalz.com/10.01.06.00413>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSGA (1.5 Folds) > FSGA 22 NK-45 G1/8-IG

Bellows suction cup (round) with optimal adaptation to uneven surfaces



Size: 22

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A


Nipple material: Aluminum

Connection: G1/8"-F

Number of folds: 1.5

Vacuum connection: G1/8"-F

Design Data



Attribute	Value
d2	11.70 mm
Dmax(S)	25 mm
dn	3.50 mm
Ds	21.50 mm
G1	G1/8"-F
H	31 mm
LG1	8 mm
SW1	14 mm
Z (Stroke)	6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction cup material	Natural Rubber NK
Material hardness [Shore A]	45 Shore A
Size	22
Number of folds	1.50
Connection	G1/8-IG
Curve radius (min) (convex)	25 mm
Volume	1.40 cm ³

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Bellows suction cups (round)

FSGA 22 NK-45 G1/8-IG

Part no.:10.01.06.00413

<https://www.schmalz.com/10.01.06.00413>

Suction force (-600mbar)	5.70 N
Pull-off force	15.20 N
Hose diameter (rec.) d	4 mm
Weight	6.20 g
Product family	FSGA

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N016 G1/8-AG DN350

Part no.:10.01.06.05735

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



FGA 22 NK-45 N016

Part no.:10.01.06.00425

Size: 22

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A

Number of folds: 1.5

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr