

Bellows suction cup SI-HD (round)

SPB4f 50 SI-HD-65 SC090

Part no.:10.01.06.03564

<https://www.schmalz.com/10.01.06.03564>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > SPB4f 50 SI-HD-65 SC090

Bellows suction cup (round) for very uneven workpieces




Size: 50

Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Number of folds: 4.5

Design Data



Attribute	Value
d	20 mm
d1	24.80 mm
d2	21 mm
D1	41.60 mm
Dk	31 mm
Dmax(S)	52 mm
Ds	49.70 mm
H	65 mm
H2	14 mm
H3	16 mm
Z (Stroke)	26 mm

Technical Data

Attribute	Value
Suction force at -200 mbar	13.70 N
Suction force at -400 mbar	27.30 N
Suction force (-600mbar)	41 N
Volume	33.11 cm ³
Size	50
Nipple family	SC 090

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr



Bellows suction cup SI-HD (round)

SPB4f 50 SI-HD-65 SC090

Part no.:10.01.06.03564

<https://www.schmalz.com/10.01.06.03564>

Number of folds	4.50
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65 Shore A
Weight	22.60 g
Product family	SPB4f

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr