

Bellows suction cups (round)

SFB1 10 EPDM-45 M5-AG

Part no.:10.01.06.04392

<https://www.schmalz.com/10.01.06.04392>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Suction Cups SFF / SFB1 > SFB1 10 EPDM-45 M5-AG

Bellows suction cup (round) for very uneven workpieces flexible workpieces




Size: 10

Suction cup material: EPDM

Material hardness [Shore A]: 45 Shore A

Design Data



Attribute	Value
Dmax(S)	11 mm
Ds	10 mm
d2	4.20 mm
dn	1.80 mm
G1	M5-AG
LG1	4.70 mm
H	17.30 mm
SW1	8 mm
Z (Stroke)	2.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	0.50 N
Volume	0.30 cm ³
Size	10
Number of folds	1.50
Suction cup material	EPDM
Material hardness [Shore A]	45 Shore A
Product family	SFB1

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Bellows suction cups (round)

SFB1 10 EPDM-45 M5-AG

Part no.:10.01.06.04392

<https://www.schmalz.com/10.01.06.04392>

Spare parts



SFB1 10 EPDM-45 SC030

Part no.:10.01.06.04373

Size: 10

Suction cup material: EPDM

Material hardness [Shore A]: 45 Shore A

Number of folds: 1.5



SC 030 M5-AG

Part no.:10.01.06.02802

Connection geometry: 030

Connection: M5-M

Length L1: 15.5 mm

Fitting length: 5 mm

Nominal diameter dn: 1.8 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr