

Vacuum block

VCBL-R 160x160x45 40x40 TV

Part no.:10.01.12.02671

<https://www.schmalz.com/10.01.12.02671>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Grid Table Systems > Vacuum block VCBL-R > VCBL-R 160x160x45 40x40 TV

Vacuum block for grid tables



Dimensions (LxB): 160 x 160

Length L: 160 mm

Width B: 160 mm


Height H: 45 mm

Grid: 40x40

Recommended slot width x slot depth [mm]: 6,5x6,5 / 7,5x7,5 mm

Add. function: Sensing valve

Design Data



Attribute	Value
B	160 mm
H	45 mm
L	160 mm

Technical Data

Attribute	Value
Grid	40x40
Weight	0.85 kg

Spare parts

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Vacuum block

VCBL-R 160x160x45 40x40 TV

Part no.:10.01.12.02671

<https://www.schmalz.com/10.01.12.02671>



TV D9 4.3

Part no.:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm



ERS VCBL-R Winkel

Part no.:10.01.12.02691



ERS VCBL-R

Part no.:10.01.12.02693

Contact Schmalz


Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr

Vacuum block

VCBL-R 160x160x45 40x40 TV

Part no.:10.01.12.02671

<https://www.schmalz.com/10.01.12.02671>



ISDR 120x120x13.5 R 30/40


Part no.:10.01.15.00353

Length L: 120 mm

Width B: 120 mm

Height H: 13.5 mm

Type: R 30/40



DR 188/180x6 MOS NK-20

Part no.:10.01.12.02901

External diameter D: 188 mm

Internal diameter d: 180 mm

Length L: 6 mm

Width B: 4 mm

Height H: 6 mm

Material type: Foam rubber

Sealing material: Natural Rubber NK

Material hardness [Shore A]: 20 Shore A

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr