

Friction plate

ISRPL 66x26x8.5


Part no.:10.01.15.00018

<https://www.schmalz.com/10.01.15.00018>



Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Accessories and Spare Parts > ISRPL 66x26x8.5

Friction plate




Width B: 26 mm

Height H: 8.5 mm

Length L: 66 mm

Type: Cup 2

Design Data



Attribute	Value
B	26 mm
H	8.50 mm
L	66 mm

Spare parts

Friction plate

ISRPL 66x26x8.5

Part no.:10.01.15.00018

<https://www.schmalz.com/10.01.15.00018>



SIEB 11x1 MS-A2 100

Part no.:10.07.01.00085

External diameter D: 11 mm

Length L: 1 mm

Material: MS-A2

Filter pore size: 100 µm

Material: Brass / Stainless steel

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8624031
schmalz@schmalz.co.kr