

## Flange plate (round)

FLAN-PL 55x7.5-AB1

Part no.:10.01.30.00015

<https://www.schmalz.com/10.01.30.00015>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Thin Glass Grippers > Accessories  
STGG > FLAN-PL 55x7.5-AB1

### Flange plate (round)




External diameter D: 55 mm

Length L: 7.5 mm

Size: AB1

### Design Data



| Attribute | Value   |
|-----------|---------|
| d         | 10 mm   |
| d1        | 4.30 mm |
| D2        | 14 mm   |
| D         | 55 mm   |
| Dmk       | 20 mm   |
| D mk1     | 46 mm   |
| G2        | M4-F    |
| L         | 7.50 mm |
| L1        | 9.50 mm |
| L2        | 2 mm    |

### Technical Data

| Attribute                           | Value |
|-------------------------------------|-------|
| Pressure range (operating pressure) | bar   |
| Weight                              | 36 g  |

### Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8962403  
schmalz@schmalz.co.kr