

Area Gripping System


STGG 170x105 QCM PEEK

Part no.:10.01.30.00520

<https://www.schmalz.com/10.01.30.00520>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Thin Glass Grippers > Thin Glass Grippers STGG > STGG 170x105 QCM PEEK

Special area gripper for gentle and extremely dynamic handling of sensitive work pieces



Length L: 170 mm


Width B: 105 mm

Height H: 67.4 mm

Add. function: Flange module QCM

Material: Polyetheretherketon

Design Data



Attribute	Value
B	105 mm
d	12 mm
d2	14 mm
D2	112 mm
Dmk	46 mm
G1	G1/8"-F
G2	M4-F
G4	M4-M
H	67.40 mm
H2	10.50 mm
H3	56.90 mm
L	170 mm
LG4	7.60 mm
W	20 °
X1	55 mm
Y1	120 mm

Technical Data

Attribute	Value
Holding force	N
Suction rate	l/min

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Area Gripping System

STGG 170x105 QCM PEEK

Part no.:10.01.30.00520

<https://www.schmalz.com/10.01.30.00520>

Air consumption	... l/min
Flow rate max.	20 m³/h
Pressure range (operating pressure)	bar
Operating temperature	5 ... 60 °C
Weight	475 g
Product family	STGG

Accessories



FLAN-PL 55x7.5-AB1

Part no.:10.01.30.00015

External diameter D: 55 mm

Length L: 7.5 mm

Size: AB1



FLAN-PL 55x7.5-EL1

Part no.:10.01.30.00208

External diameter D: 55 mm

Length L: 7.5 mm

Size: EL1

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr

Area Gripping System

STGG 170x105 QCM PEEK

Part no.:10.01.30.00520

<https://www.schmalz.com/10.01.30.00520>



FLAN-PL 55x9.5-JP1

Part no.:10.01.30.00194

External diameter D: 55 mm

Length L: 9.5 mm

Size: JP1

Thread G1: G3/8"-F



FLAN-PL 63x10.5-AD1

Part no.:10.01.30.00016

External diameter D: 63 mm

Length L: 10.5 mm

Size: AD1



FLAN-PL 63x11.5-UNI

Part no.:10.01.30.00017

External diameter D: 63 mm

Length L: 11.5 mm

Size: UNI

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8562431
schmalz@schmalz.co.kr

Area Gripping System

STGG 170x105 QCM PEEK

Part no.:10.01.30.00520

<https://www.schmalz.com/10.01.30.00520>



FLAN-PL 80x12-ST1

Part no.:10.01.30.00167

External diameter D: 80 mm

Length L: 12 mm

Size: ST1



HTR M12x1-IG SWGm

Part no.:10.01.30.00119

Width B: 14 mm

Length L: 30.9 mm

Thread G1: M12x1-F

Construction use: Wafer gripper



HTR M8x1-IG SWGm

Part no.:10.01.30.00118

Width B: 14 mm

Length L: 30.9 mm

Thread G1: M8x1-F

Construction use: Wafer gripper

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Area Gripping System

STGG 170x105 QCM PEEK

Part no.:10.01.30.00520

<https://www.schmalz.com/10.01.30.00520>



HTR-UNI SWGm

Part no.:10.01.30.00117

Width B: 14 mm

Length L: 30.9 mm

Construction use: Wafer gripper

Cross-beam connection: Universal holder



SBSm 14 90-3 4/2 0

Part no.:10.01.01.12912

Width B: 14 mm

Number of holes: 3

Length L: 30.85 mm

Angle of radiation: 90 °

Connection: Hose 4/2

Slewing angle W: 0 °



SD-MOD 4 32x15x35 FG 9 SWGm

Part no.:10.01.30.00121

Width B: 15 mm

Length L: 32 mm

Construction use: Wafer gripper

Spare parts

Contact Schmalz


Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Area Gripping System

STGG 170x105 QCM PEEK

Part no.:10.01.30.00520

<https://www.schmalz.com/10.01.30.00520>



STGG 170x105x26.9 QCFA PEEK

Part no.:10.01.30.00478

Length L: 170 mm

Width B: 105 mm

Height H: 26.9 mm

Add. function: Quick-change adapter

Material: Polyetheretherketon

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8524031
schmalz@schmalz.co.kr