

Suction cup (round)

SAUG-SCGS 50 NBR-ESD-55

Part no.:10.01.30.00915

<https://www.schmalz.com/10.01.30.00915>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Flow Grippers > Suction Cups for Flow Grippers SCGS > SAUG-SCGS 50 NBR-ESD-55

Suction cup (round)



Size: 50

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
D1	51 mm
Dmax (N)	25 mm
Dmax(S)	51.50 mm
dn	18.90 mm
Ds	50.30 mm
G1	M20x1-F
H	31.50 mm
LG1	5 mm
Z (Stroke)	4.20 mm

Technical Data

Attribute	Value
Size	50
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55 Shore A
Weight	24.30 g
Product family	SAUG-SCGS

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Suction cup (round)

SAUG-SCGS 50 NBR-ESD-55

Part no.:10.01.30.00915

<https://www.schmalz.com/10.01.30.00915>

Spare parts



FLSA 50 NBR-ESD-55

Part no.:10.01.06.04388

Size: 50

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8624031
schmalz@schmalz.co.kr