

Vacuum pump

EVE-TR 360 AC3 IE3-TYP1 F

Part no.:10.03.01.00270

<https://www.schmalz.com/10.03.01.00270>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Pumps > Dry-Running Vacuum Pumps EVE-TR > EVE-TR 360 AC3 IE3-TYP1 F

Oil-free pump with constant suction rate, robust, requires little maintenance



Current type: three-phase current

Sound level at 50 Hz: 80.5 dB(A)

Voltage at 50Hz: D400V $\pm 10\%$

Voltage at 60Hz: D460V $\pm 10\%$

Suction rate (50 Hz): 351 m³/h

Suction rate (60 Hz): 402 m³/h

Vacuum (50 Hz): -750 mbar

Rated power 50 Hz: 11 kW


Rated power 60 Hz: 13.2 kW

Construction: IE3:EU/CN/IND

with: Filter

Weight: 256.5 kg

Design Data



Attribute	Value
B	644 mm
B2	116 mm
G3	G2-1/2"-F
G5	M10-F
H	528 mm
L	1180 mm
L2	124 mm
X1	645 mm
Y1	380 mm
Y2	190 mm

Technical Data

Attribute	Value
Suction rate (50 Hz)	351 m ³ /h
Suction rate (60 Hz)	402 m ³ /h
Voltage at 50Hz	D400V $\pm 10\%$
Voltage at 60Hz	D460V $\pm 10\%$
Rated power 50 Hz	11 kW
Rated power 60 Hz	13.20 kW

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Vacuum pump

EVE-TR 360 AC3 IE3-TYP1 F


Part no.:10.03.01.00270

<https://www.schmalz.com/10.03.01.00270>

Current type	AC3
Current type	three-phase current
Construction	IE3:EU/CN/IND
Sound level at 50 Hz	80.50 dB(A)
Weight	256.50 kg
Protection type IP	IP 55
Product family	EVE-TR

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

Spare parts



VST EVE-TR-360

Part no.:10.03.01.00187

Construction use: Pump EVE-TR

Size: 360

contains: Brush slide/Filter



FILT-EINS EVE-TR-250/360

Part no.:10.03.01.00188

Construction use: Pump EVE-TR

Size: 250/360

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr