

Flange plate robot application

FLAN-PL UR-KUK-1

Part no.:10.03.01.00313

<https://www.schmalz.com/10.03.01.00313>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Generators End-of-Arm > FLAN-PL UR-KUK-1

Flange plate (round)




Length L: 13 mm

Type: UR-KUK-1

Type: 3,5,10-iiwa7,14

Design Data



Attribute	Value
d	27.50 mm
d1	6.60 mm
D	63.50 mm
D mk1	50 mm
D2	31.50 mm
L	13 mm
L1	18 mm

Accessories

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Flange plate robot application

FLAN-PL UR-KUK-1

Part no.:10.03.01.00313

<https://www.schmalz.com/10.03.01.00313>



ECBPi 12 24V-DC M12-8

Part no.:10.03.01.00314

Suction rate (max.): 12 l/min

Rated power: 13 W

Voltage DC: 24V - DC

Rated current: 0.6 A

Electrical connection: Male connect M12, 8 pol

Max. vacuum: 750 mbar

Operating temperature: 5 ... 45 °C



ECBPi 12 24V-DC TB-8

Part no.:10.03.01.00364

Suction rate (max.): 12 l/min

Rated power: 13 W

Voltage DC: 24V - DC

Rated current: 0.6 A

Electrical connection: Terminal block 8x

Max. vacuum: 750 mbar

Operating temperature: 5 ... 45 °C

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr