

Vacuum pump

EVE-TR 40 AC3 IE3-TYP2 F

Part no.:10.03.01.00354

<https://www.schmalz.com/10.03.01.00354>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Pumps > Dry-Running Vacuum Pumps EVE-TR > EVE-TR 40 AC3 IE3-TYP2 F

Oil-free pump with constant suction rate, robust, requires little maintenance



Current type: three-phase current

Voltage at 60Hz: YY230/Y460V $\pm 10\%$

Suction rate (60 Hz): 48 m³/h

Rated power 60 Hz: 1.3 kW


Construction: IE3:US/CAN

with: Filter

Permission: UL/CSA

Weight: 42 kg

Design Data



Attribute	Value
B	270 mm
B2	50 mm
d	7 mm
G2	G1-1/4"-F
G3	G3/4"-F
H	293 mm
H1	421 mm
H2	70 mm
L	561 mm
L2	131 mm
X1	220 mm
Y1	190 mm

Technical Data

Attribute	Value
Suction rate (60 Hz)	48 m ³ /h
Voltage at 60Hz	YY230/Y460V $\pm 10\%$
Rated power 60 Hz	1.30 kW
Current type	AC3
Current type	three-phase current
Construction	IE3:US/CAN

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr



Vacuum pump

EVE-TR 40 AC3 IE3-TYP2 F

Part no.:10.03.01.00354

<https://www.schmalz.com/10.03.01.00354>

Weight	42 kg
Protection type IP	IP 55
Product family	EVE-TR

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8624031
schmalz@schmalz.co.kr