

Solenoid valve

EMV 15 230V-AC 3/2 NO

Part no.:10.05.01.00073

<https://www.schmalz.com/10.05.01.00073>

Home > Vacuum Technology for Automation > Vacuum Components > Valve Technology > Solenoid Valves > Solenoid Valves
EMV > EMV 15 230V-AC 3/2 NO

Solenoid valve EMV for direct control of vacuum and compressed air



Nominal size: 15 mm

Voltage DC: 230V - AC

Function: 3/2-way valve


Control valve: Normally open

Connecting thread: G3/4\"-F

Pressure range (operating pressure): bar

Power consumption DC: 38.4 W

Design Data



Attribute	Value
d	6.50 mm
D	80 mm
G1	G3/4\"-F
G2	G3/4\"-F
G3	G3/4\"-F
H	114 mm
H1	140 mm
L	209 mm
L1	211 mm
X1	133 mm
Y1	40 mm

Technical Data

Attribute	Value
Nominal size	15 mm
Control valve	Normally open
Nominal flow rate	566.70 l/min
Nominal flow rate	34 m³/h
Power consumption DC	38.40 W
Voltage DC	230V - AC

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Solenoid valve


EMV 15 230V-AC 3/2 NO

Part no.:10.05.01.00073

<https://www.schmalz.com/10.05.01.00073>

Closing time	80 ms
Weight	4.67 kg
Product family	EMV

Accessories



FAS 80x39 G3/4-AG


Part no.:10.05.01.00062

External diameter D: 80 mm

Length L: 39 mm

Thread G1: G3/4"-M

Spare parts



FAS 80x39 G3/4-AG

Part no.:10.05.01.00062

External diameter D: 80 mm

Length L: 39 mm

Thread G1: G3/4"-M

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr