

Solenoid valve


EMV 25 24V-DC 3/2 NO

Part no.:10.05.01.00076

<https://www.schmalz.com/10.05.01.00076>

Home > Vacuum Technology for Automation > Vacuum Components > Valve Technology > Solenoid Valves > Solenoid Valves
EMV > EMV 25 24V-DC 3/2 NO

Solenoid valve EMV for direct control of vacuum and compressed air



Nominal size: 25 mm

Voltage DC: 24V - DC

Function: 3/2-way valve


Control valve: Normally open

Connecting thread: G1-1/4"-F

Pressure range (operating pressure): bar

Power consumption DC: 63.8 W

Design Data



Attribute	Value
d	8.50 mm
D	80 mm
G1	G1-1/4"-F
G2	G1-1/4"-F
G3	G1-1/4"-F
H	167 mm
H1	200 mm
L	281 mm
L1	271.50 mm
X1	178 mm
Y1	50 mm

Technical Data

Attribute	Value
Nominal size	25 mm
Control valve	Normally open
Nominal flow rate	1,466.70 l/min
Nominal flow rate	88 m³/h
Power consumption DC	63.80 W
Voltage DC	24V - DC

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Solenoid valve


EMV 25 24V-DC 3/2 NO

Part no.:10.05.01.00076

<https://www.schmalz.com/10.05.01.00076>

Closing time	135 ms
Weight	9.60 kg
Product family	EMV

Accessories



FAS 80x32 G1-1/4-AG EMVP-25+50

Part no.:10.05.01.00064

External diameter D: 80 mm


Length L: 32 mm

Thread G1: G1-1/4"-M

Construction use: Solenoid valve

Size: 25+50

Spare parts



FAS 80x32 G1-1/4-AG EMVP-25+50

Part no.:10.05.01.00064

External diameter D: 80 mm

Length L: 32 mm

Thread G1: G1-1/4"-M

Construction use: Solenoid valve

Size: 25+50

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr