

Plug connector, T

SVB-T 8

Part no.:10.09.02.00022

<https://www.schmalz.com/10.09.02.00022>


Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > SVB-T 8

Plug connection, T



Hose diameter: 8 mm
Material: Brass
Operating temperature: -20 ... 80 °C
Length L: 49 mm

Design Data



Attribute	Value
d	8 mm
D1	14.40 mm
H	24.70 mm
H1	31.90 mm
L	49 mm

Technical Data

Attribute	Value
Hose type	Hose D = 8 d = 6
Hose type	8-6
Material	Brass
Pressure range (operating pressure)	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Weight	43 g
Product family	STV


Plug connector, T

SVB-T 8

Part no.:10.09.02.00022

<https://www.schmalz.com/10.09.02.00022>

Accessories



VSL 8-6 PE BL

Part no.:10.07.09.00015

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 8-6 PU MI-TR

Part no.:10.07.09.00003

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 45 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -35 ... 60 °C

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr