

Plug union, T

STV-T G1/4-AG 10

Part no.:10.09.02.00044

<https://www.schmalz.com/10.09.02.00044>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-T G1/4-AG 10

Push-in Fitting, T



Thread G1: G1/4"-M


Hose diameter: 10 mm

Material: Brass

Operating temperature: °C

Length L: 54.9 mm

Design Data



Attribute	Value
d	10 mm
G1	G1/4"-M
dn	8 mm
D1	16.50 mm
H	15 mm
H1	23.20 mm
L	54.90 mm
LG1	7.60 mm
SW1	17 mm

Technical Data

Attribute	Value
Hose type	Hose D = 10 d = 7
Hose type	10-7
Material	Brass
Pressure range (operating pressure)	bar
Operating temperature	°C
Weight	70.30 g
Product family	STV

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Plug union, T

STV-T G1/4-AG 10

Part no.:10.09.02.00044

<https://www.schmalz.com/10.09.02.00044>

Accessories



VSL 10-7 PE MI-TR

Part no.:10.07.09.00083

External diameter D: 10 mm

Internal diameter d: 7 mm

Length max.: 50 m

Material hose: PE

Bending radius min.: 60 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -30 ... 70 °C



VSL 10-7 PU MI-TR

Part no.:10.07.09.00084

External diameter D: 10 mm

Internal diameter d: 7 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 60 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -40 ... 85 °C

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr