

Plug connector, T

SVB-T 14

Part no.:10.09.02.00046

<https://www.schmalz.com/10.09.02.00046>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > SVB-T 14

Plug connection, T




Hose diameter: 14 mm

Material: Brass

Operating temperature: °C

Length L: 72 mm

Design Data



Attribute	Value
d	14 mm
D1	21.30 mm
H	36 mm
H1	46.50 mm
L	72 mm

Technical Data

Attribute	Value
Hose type	Hose D = 14 d = 11
Hose type	14-11
Material	Brass
Pressure range (operating pressure)	bar
Operating temperature	°C
Weight	141.70 g
Product family	STV

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Plug connector, T

SVB-T 14

Part no.:10.09.02.00046

<https://www.schmalz.com/10.09.02.00046>

Accessories



VSL 14-11 PU MI-TR

Part no.:10.07.09.00038

External diameter D: 14 mm

Internal diameter d: 11 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 100 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr