

Flat suction cup (round)

SG 16 SI-55 N026

Part no.:10.01.01.00602

<https://www.schmalz.com/10.01.01.00602>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Different Industries > SG 16 SI-55 N026

Flat suction cup (round)



Size: 16

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Height H: 20 mm

Design Data



Attribute	Value
d	5 mm
Dk	8 mm
Dmax(S)	17.50 mm
Ds	16 mm
H	20 mm
H2	12 mm
Z (Stroke)	4 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Number of folds	0
Size	16
Suction cup material	Silicone SI
Suction force (-600mbar)	8 N
Material hardness [Shore A]	55 Shore A
Product family	SG

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Flat suction cup (round)

SG 16 SI-55 N026

Part no.:10.01.01.00602

<https://www.schmalz.com/10.01.01.00602>

Accessories



SA-NIP N026 M5-AG DN200

Part no.:10.01.01.00319

Thread G1: M5-M

Fitting length: 3 mm

Material: Aluminum

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr