

Suction cup cover

SU 40

Part no.:10.01.01.12856

<https://www.schmalz.com/10.01.01.12856>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Accessories Vacuum Suction Cups > Suction Cup Covers SU > SU 40

Cover for suction cup



Size: 40

Clamping range: 35.0 ... 45.0 mm

Temperature resistance: 80 °C

Design Data



Attribute	Value
d	5 mm
D	47 mm
D2	30 mm

Technical Data

Attribute	Value
Size	40
Clamping range	35.0 ... 45.0 mm
Weight	0.50 g
Product family	SU

Note: In vertical applications with a suction plate or cup, the lateral force sinks by up to 70%. The vacuum generator must be able to provide 10% more suction power

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr