

Ball joint

KGL G1/8-IG G1/8-AG A2

Part no.:10.01.03.00109

<https://www.schmalz.com/10.01.03.00109>

Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Jointed Mountings > Ball Joints
KGL > KGL G1/8-IG G1/8-AG A2

Suction cup mounting with joint for adaptation to sloping surfaces




Thread G1: G1/8"-F

Thread G2: G1/8"-M

Height H: 26.5 mm

Material: Aust. Stainless steel

Design Data



Attribute	Value
dn	2 mm
H	26.50 mm
G1	G1/8"-F
G2	G1/8"-M
LG1	8.50 mm
LG2	7 mm
SW1	14 mm
W	15 °

Technical Data

Attribute	Value
Vertical load	300 N
Weight	26 g
Product family	KGL

Spare parts

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Ball joint

KGL G1/8-IG G1/8-AG A2

Part no.:10.01.03.00109

<https://www.schmalz.com/10.01.03.00109>



DR G1/8 15/10x1.5 PA

Part no.:10.07.08.00020

for: G1/8

External diameter D: 15 mm

Internal diameter d: 10 mm

Material: Polyamide

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8624031
schmalz@schmalz.co.kr