

Flat suction cup (oval)

SGO 24x8 SI-HD-65 N022

Part no.:10.01.05.01036

<https://www.schmalz.com/10.01.05.01036>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > SGO 24x8 SI-HD-65 N022


Flat suction cup (oval) for narrow or curved workpieces



Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Design Data



Attribute	Value
Bmax(S)	9 mm
Bs	7.60 mm
d	5.50 mm
d1	7 mm
dn	1.50 mm
Dk	11.50 mm
Lmax(S)	24.50 mm
Ls	23.60 mm
H	12 mm
H2	3 mm
H3	5.50 mm
Z (Stroke)	1 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	8 N
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65 Shore A
Weight	2.60 g
Product family	SGO

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr

Flat suction cup (oval)

SGO 24x8 SI-HD-65 N022

Part no.:10.01.05.01036

<https://www.schmalz.com/10.01.05.01036>

Accessories



SA-NIP N022 G1/8-AG DN350

Part no.:10.01.05.00124

Thread G1: G1/8"-M

Length L1: 18.5 mm

Fitting length: 5 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



SA-NIP N022 G1/8-IG DN350

Part no.:10.01.05.00123

Thread G1: G1/8"-F

Length L1: 18.5 mm

Fitting length: 13 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr