

Flat suction cup (oval)

SGO 60x20 SI-HD-65 N023

Part no.:10.01.05.01039

<https://www.schmalz.com/10.01.05.01039>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > SGO 60x20 SI-HD-65 N023


Flat suction cup (oval) for narrow or curved workpieces



Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Design Data



Attribute	Value
Bmax(S)	22 mm
Bs	19 mm
d	11.50 mm
d1	13 mm
dn	4 mm
Dk	15.50 mm
Lmax(S)	61 mm
Ls	59 mm
H	21 mm
H2	8 mm
H3	10 mm
Z (Stroke)	2.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	50.10 N
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65 Shore A
Weight	9.70 g
Product family	SGO

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Flat suction cup (oval)

SGO 60x20 SI-HD-65 N023

Part no.:10.01.05.01039

<https://www.schmalz.com/10.01.05.01039>

Accessories



SA-NIP N023 G1/4-AG DN350

Part no.:10.01.05.00122

Thread G1: G1/4"-M

Length L1: 25 mm

Fitting length: 5 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



SA-NIP N023 G1/4-IG DN350

Part no.:10.01.05.00121

Thread G1: G1/4"-F

Length L1: 25 mm

Fitting length: 15 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr