

Flange plate (round)

FLAN-PL 63x10.5-AD1

Part no.:10.01.30.00016

<https://www.schmalz.com/10.01.30.00016>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Thin Glass Grippers > Accessories
STGG > FLAN-PL 63x10.5-AD1

Flange plate (round)




External diameter D: 63 mm

Length L: 10.5 mm

Size: AD1

Design Data



Attribute	Value
d	25 mm
d1	6.60 mm
D2	41.10 mm
D	63 mm
Dmk	46 mm
D mk1	50 mm
G2	M4-F
L	10.50 mm
L1	13.50 mm
L2	3 mm
L3	3 mm

Technical Data

Attribute	Value
Pressure range (operating pressure)	bar
Weight	57.50 g

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr