

Flange module

VEE-QCM 53

Part no.:10.01.36.00122

<https://www.schmalz.com/10.01.36.00122>


Home > Vacuum Technology for Automation > Vacuum Components > Area Gripping Systems and End Effectors > Vacuum End Effectors VEE > Flange Modules VEE-QCM > VEE-QCM 53

VEE flange module with quick-change adapter and integrated vacuum line



Length L1: 53 mm
Thread G1: G1/8"-F
Pitch diameter D mk: 46 mm
Number of holes: 8
Flow rate max.: 20 m³/h

Design Data



Attribute	Value
D	25.40 mm
D1	55 mm
d2	12 mm
Dmk	46 mm
G1	G1/8"-F
G2	M4-M
L	40 mm
L1	53 mm
LG2	7.60 mm

Technical Data

Attribute	Value
Connection	Bayonet connection

Accessories

Flange module

VEE-QCM 53

Part no.:10.01.36.00122

<https://www.schmalz.com/10.01.36.00122>



EMV 1.5 24V-DC 3/2 NC K-2P

Part no.:10.05.01.00288

Nominal size: 1.5 mm

Voltage DC: 24V - DC

Function: 3/2-way valve

Control valve: Normally closed

Connecting thread: M5-M

Pressure range (operating pressure): 3.5 ... 7.0 bar

Interface electrical connection: Cable, 2 pol



FLAN-PL 55x7.5-AB1

Part no.:10.01.30.00015

External diameter D: 55 mm

Length L: 7.5 mm

Size: AB1



FLAN-PL 55x7.5-EL1

Part no.:10.01.30.00208

External diameter D: 55 mm

Length L: 7.5 mm

Size: EL1

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Flange module

VEE-QCM 53

Part no.:10.01.36.00122

<https://www.schmalz.com/10.01.36.00122>



FLAN-PL 55x9.5-JP1

Part no.:10.01.30.00194

External diameter D: 55 mm

Length L: 9.5 mm

Size: JP1

Thread G1: G3/8"-F



FLAN-PL 63x10.5-AD1

Part no.:10.01.30.00016

External diameter D: 63 mm

Length L: 10.5 mm

Size: AD1



FLAN-PL 63x11.5-UNI

Part no.:10.01.30.00017

External diameter D: 63 mm

Length L: 11.5 mm

Size: UNI

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8562431
schmalz@schmalz.co.kr

Flange module

VEE-QCM 53

Part no.:10.01.36.00122

<https://www.schmalz.com/10.01.36.00122>



FLAN-PL 80x12-ST1

Part no.:10.01.30.00167

External diameter D: 80 mm

Length L: 12 mm

Size: ST1



RFBP 50 50 BA SPB2

Part no.:10.01.45.00096

Length L: 50 mm

Width B: 50 mm

Connection: Bayonet connection

Suct. cups: Bellows suct. cup SPB2



RFBP 100 58 BA SPB2

Part no.:10.01.45.00091

Length L: 100 mm

Width B: 58 mm

Connection: Bayonet connection

Suct. cups: Bellows suct. cup SPB2

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8962403
schmalz@schmalz.co.kr

Flange module

VEE-QCM 53

Part no.:10.01.36.00122

<https://www.schmalz.com/10.01.36.00122>



RFBP 100 58 BA O10

Part no.:10.01.45.00092

Length L: 100 mm

Width B: 58 mm

Connection: Bayonet connection

Material type: Foam O, Height 10 mm



RFBP 120 120 BA SPB2

Part no.:10.01.45.00085

Length L: 120 mm

Width B: 120 mm

Connection: Bayonet connection

Suct. cups: Bellows suct. cup SPB2



RFBP 120 120 BA O10

Part no.:10.01.45.00086

Length L: 120 mm

Width B: 120 mm

Connection: Bayonet connection

Material type: Foam O, Height 10 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr