

Solenoid valve pressure

EMV 2.5 24V-DC 3/2 NC K-2P

Part no.:10.05.01.00289

<https://www.schmalz.com/10.05.01.00289>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Thin Glass Grippers > Accessories
STGG > EMV 2.5 24V-DC 3/2 NC K-2P

Solenoid valve EMV for direct control of compressed air



Nominal size: 2.5 mm

Voltage DC: 24V - DC

Function: 3/2-way valve


Control valve: Normally closed

Connecting thread: G1/8"-M

Pressure range (operating pressure): 3.5 ... 7.0 bar

Interface electrical connection: Cable, 2 pol

Design Data



Attribute	Value
B1	31.70 mm
B2	10.70 mm
d	4 mm
G1	G1/8"-M
G2	M5-F
L	51.70 mm
L1	56.50 mm

Technical Data

Attribute	Value
Nominal size	2.50 mm
Control valve	Normally closed
Nominal flow rate	135 l/min
Nominal flow rate	8.10 m ³ /h
Voltage DC	24V - DC
Weight	0.10 kg
Product family	EMV

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr



Solenoid valve pressure

EMV 2.5 24V-DC 3/2 NC K-2P

Part no.:10.05.01.00289

<https://www.schmalz.com/10.05.01.00289>

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr