

Vacuum/pressure switch

VSi V D M8-4

Part no.:10.06.02.00577

<https://www.schmalz.com/10.06.02.00577>

Home > Vacuum Technology for Automation > Vacuum Components > Switches and System Monitoring > Electronic Vacuum and Pressure Switches > Vacuum and Pressure Switches VSi > VSi V D M8-4

Universal vacuum and pressure switch with IO-Link function



Measuring range: -1,0 ... 0,0 bar


Construction shape vacuum switch: with display

Electrical connection: Male connect M8, 4 pole

Indication: 2xLED

Protection type IP: IP 65

Design Data



Attribute	Value
D	19.60 mm
G1	G1/8"-M
G2	M5-F
G3	M8x1-M
L	60.50 mm
L1	77.50 mm
LG1	8 mm

Technical Data

Attribute	Value
Measured medium	Non-aggressive gases; dry, oil-free air
Measuring range	-1,0 ... 0,0 bar
Overpressure resistance	8 bar
Measuring range	-14.5 ... 0.0 psi psi
Overpressure resistance	116.03 psi
Repeatability	± 3% of full-scale value
Hysteresis	Adjustable
Inputs/outputs	2 digital

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Vacuum/pressure switch

VSi V D M8-4

Part no.:10.06.02.00577

<https://www.schmalz.com/10.06.02.00577>

Switching capacity (max)	100 mA
Indication	2xLED
Electrical connection	Male connect M8, 4 pole
Connection	G1/8"-M + M5-F
Voltage	10-30V DC
Current consumption	35 mA
Protection type IP	IP 65
Operating temperature	0 ... 50 °C
Weight	16 g
Construction shape vacuum switch	with display
Product family	VSi

Accessories



ASK B-M8-4 5000 K-4P

Part no.:10.06.02.00031

Electrical connection: Fem connect M8, 4 pol

Cable length: 5,000 mm

Material hose: PUR cable



ASK WB-M8-4 5000 K-4P

Part no.:10.06.02.00032

Electrical connection: Elbow fem con M8, 4 pol

Cable length: 5,000 mm

Material hose: PUR cable

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr

Vacuum/pressure switch

VSi V D M8-4

Part no.:10.06.02.00577

<https://www.schmalz.com/10.06.02.00577>



BEF-WIN 21x22x60.5 1.5 VS

Part no.:10.06.02.00061

Length L: 60.5 mm

Width B: 21 mm

Height H: 22 mm

Wall thickness s: 1.5 mm

Construction use: Vacuum switch



STVI-GE G1/8-IG 4

Part no.:10.08.02.00149

Thread G1: G1/8"-F

Hose diameter: 4 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 8.5 mm

Length L: 23.5 mm



STVI-GE G1/8-IG 6

Part no.:10.08.02.00150

Thread G1: G1/8"-F

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11.5 mm

Length L: 26.5 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624831
schmalz@schmalz.co.kr

Vacuum/pressure switch

VSi V D M8-4

Part no.:10.06.02.00577

<https://www.schmalz.com/10.06.02.00577>



STVI-GE G1/8-IG 8

Part no.:10.08.02.00151

Thread G1: G1/8"-F

Hose diameter: 8 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 14.5 mm

Length L: 29.5 mm



HTR-VSi Clip

Part no.:10.06.02.00718

Width B: 12 mm

Height H: 25.3 mm

Length L: 20 mm

Construction use: Vacuum/pressure switch



BEF-WIN 21x22x61.5 1.5 VSi-D-M8

Part no.:10.06.02.00664

Width B: 21 mm

Height H: 22 mm

Length L: 61.5 mm

Wall thickness s: 1.5 mm

Construction use: Vacuum/pressure switch

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr