

Flat suction cup (round)

PFG 30 NBR-CO-55 N007

Part no.:10.01.01.10339

<https://www.schmalz.com/10.01.01.10339>

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 30

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d	6 mm
d1	11 mm
Dk	15.10 mm
Dmax(S)	31.50 mm
Ds	28.80 mm
H	12 mm
H2	7 mm
Z (Stroke)	2 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	34 N
Volume	1.56 cm ³
Curve radius (min) (convex)	40 mm
Size	30
Nipple family	N 007
Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55 Shore A
Weight	3.40 g

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Flat suction cup (round)

PFG 30 NBR-CO-55 N007

Part no.:10.01.01.10339

<https://www.schmalz.com/10.01.01.10339>

Product family

PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SA-NIP N007 G1/8-AG DN240

Part no.:10.01.01.03531

Nipple family: N 007

Thread G1: G1/8"-M

Length L1: 21 mm

Length L: 5 mm

Fitting length: 5 mm

Nominal diameter dn: 2.4 mm

Material: Aluminum

Spanner size SW2: 4 mm



SA-NIP N007 G1/8-IG DN350

Part no.:10.01.01.03523

Nipple family: N 007

Thread G1: G1/8"-F

Length L1: 24.5 mm

Length L: 16 mm

Fitting length: 16 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

Spanner size SW2: 4 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr

Flat suction cup (round)

PFG 30 NBR-CO-55 N007

Part no.:10.01.01.10339

<https://www.schmalz.com/10.01.01.10339>



SU 30

Part no.:10.01.01.12889

Size: 30

Clamping range: 27.0 ... 35.0 mm

Temperature resistance: 80 °C

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8624311
schmalz@schmalz.co.kr