

Cup

ISCUP Cup 2 80x40x30 TV

Part no.:10.01.15.00305

<https://www.schmalz.com/10.01.15.00305>




Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann Clamping Equipment ISCUP/ISMB/ISQB > ISCUP Cup 2 80x40x30 TV

Suction cup for Innospann



Dimensions (LxB):	80 x 40
Length L:	80 mm
Width B:	40 mm
Height H:	30 mm
Add. function:	Sensing valve

Design Data



Attribute	Value
B	40 mm
d	60 mm
H	30 mm
L	80 mm

Technical Data

Attribute	Value
Weight	0.10 kg

Spare parts

Cup

ISCUP Cup 2 80x40x30 TV

Part no.:10.01.15.00305

<https://www.schmalz.com/10.01.15.00305>



DI-PROF 4x10 MOS EPDM HR

Part no.:10.01.15.00062

Width B: 4 mm

Height H: 10 mm

Sealing material: EPDM

Material type: Foam rubber

Form: half-round



ISDR 81x43x12 Cup 2 NK-50

Part no.:10.01.15.00021

Width B: 43 mm

Height H: 12 mm

Length L: 81 mm

Suction cup material: Natural rubber NK-50

Type: Cup 2



ISRPL 66x26x8.5 NK-45 d12

Part no.:10.01.15.00344

Width B: 26 mm

Internal diameter d: 12 mm

Height H: 8.5 mm

Length L: 66 mm

Suction cup material: Natural rubber NK-45

Type: Cup 2

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr

Cup

ISCUP Cup 2 80x40x30 TV

Part no.:10.01.15.00305

<https://www.schmalz.com/10.01.15.00305>



O-RING 48x2 CR-70

Part no.:10.07.08.00468



TV D11 4.3

Part no.:10.01.15.00347

External diameter D: 11 mm

Spring stroke Z: 4.3 mm

Length L: 24 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr