

Vacuum pump

EVE-OG 63 AC3

Part no.:10.03.02.00073

<https://www.schmalz.com/10.03.02.00073>




Home > Vacuum Clamping Technology > Vacuum Generators > Vacuum Generators for CNC Machining Centers > EVE-OG 63 AC3

Oil-lubricated pump for maximum vacuum levels, requires little maintenance



- Current type: three-phase current
- Voltage at 50Hz: 200-240V or 345-420V
- Rated power 50 Hz: 1.5 kW
- Suction rate (50 Hz): 63 m³/h

Design Data



Attribute	Value
G3	G1-1/4"-F

Technical Data

Attribute	Value
Max. vacuum	-980 mbar
Rated power 50 Hz	1.50 kW
Suction rate (50 Hz)	63 m³/h
Suction rate	63 m³/h
Protection type IP	IP 54
Voltage at 50Hz	200-240V or 345-420V
Current range (50 Hz)	6.2A or 3.6A
Current type	three-phase current



Vacuum pump

EVE-OG 63 AC3

Part no.:10.03.02.00073

<https://www.schmalz.com/10.03.02.00073>

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr