

Compressed-air hose


VSL 21-12 PVC-G KL-TR

Part no.:10.07.09.00006

<https://www.schmalz.com/10.07.09.00006>

Home > Vacuum Lifters and Crane Systems > Vacuum Lifting Device VacuMaster > Spare and Wear Parts Vacuum Lifting Devices
VacuMaster > Spare and Wear Parts VacuMaster Eco > VSL 21-12 PVC-G KL-TR

Compressed-air hose



External diameter D: 21 mm

Internal diameter d: 12 mm


Length max.: 50 m

Material hose: PVC with tissue

Pressure range (operating pressure): bar

Operating temperature: °C

Design Data



Attribute	Value
d	12 mm
D	21 mm

Technical Data

Attribute	Value
Hose type	21-12
Pressure range (operating pressure)	bar
Operating temperature	°C
Length max.	50 m
Weight/Meter	297 g/m
Weight/Meter	0.30 kg/m
Material hose	PVC with tissue

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8162403
schmalz@schmalz.co.kr

Compressed-air hose

VSL 21-12 PVC-G KL-TR

Part no.:10.07.09.00006

<https://www.schmalz.com/10.07.09.00006>

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



SSB 12-22 ST-VZ

Part no.:10.07.10.00160

Clamping range: 12.0 ... 22.0 mm

Material: Steel

Surface: galvanised




SSB 16-27 ST-VZ

Part no.:10.07.10.00002

Clamping range: 16.0 ... 27.0 mm

Material: Steel

Surface: galvanised



SSB 20-32 ST-VZ

Part no.:10.07.10.00003

Clamping range: 20.0 ... 32.0 mm

Material: Steel

Surface: galvanised

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr

Compressed-air hose

VSL 21-12 PVC-G KL-TR

Part no.:10.07.09.00006

<https://www.schmalz.com/10.07.09.00006>



KAPP 9 Band

Part no.:20.12.01.00036

Length L: 9 mm

Size: Band



ST G1/2-AG 13 MS-V

Part no.:10.08.03.00162

Thread G1: G1/2"-M

Hose diameter (rec.) d: 13 mm

Material: Brass

Surface: nickel plated

Length L: 6 mm

Nominal diameter dn: 11 mm



ST G1/4-AG 13 MS-V

Part no.:10.08.03.00158

Thread G1: G1/4"-M

Hose diameter (rec.) d: 13 mm

Material: Brass

Surface: nickel plated

Length L: 5.5 mm

Nominal diameter dn: 7.5 mm

Contact Schmalz


Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8962431
schmalz@schmalz.co.kr

Compressed-air hose

VSL 21-12 PVC-G KL-TR

Part no.:10.07.09.00006

<https://www.schmalz.com/10.07.09.00006>



ST G3/4-AG 13 MS-V

Part no.:10.08.03.00164

Thread G1: G3/4"-M

Hose diameter (rec.) d: 13 mm

Material: Brass

Surface: nickel plated

Length L: 8 mm

Nominal diameter dn: 10.4 mm



ST G3/8-AG 13 MS-V

Part no.:10.08.03.00160

Thread G1: G3/8"-M

Hose diameter (rec.) d: 13 mm

Material: Brass

Surface: nickel plated

Length L: 5.9 mm

Nominal diameter dn: 10 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr