

Controller

STEU 24V-DC OFG-B

Part no.:10.01.51.00005

<https://www.schmalz.com/10.01.51.00005>

Home > Vacuum Technology for Automation > Vacuum Components > Area Gripping Systems and End Effectors > Finger Grippers > STEU 24V-DC OFG-B

Controller



Voltage DC: 24V - DC

Construction use: Finger gripper basic


Operating temperature: 0 ... 50 °C

Pressure range (operating pressure): 6.0 ... 8.0 bar

Hose type: Hose D = 8 d = 6

Weight: 1,727 g

Design Data



Attribute	Value
B	162.50 mm
d	9 mm
d1	9 mm
H	67 mm
L	275 mm
X1	260 mm
Y1	122 mm

Technical Data

Attribute	Value
Voltage DC	24V - DC
Hose type	Hose D = 8 d = 6
Pressure range (operating pressure)	6.0 ... 8.0 bar
Operating temperature	0 ... 50 °C
Weight	1727 g

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8162403
schmalz@schmalz.co.kr

Controller

STEU 24V-DC OFG-B

Part no.:10.01.51.00005

<https://www.schmalz.com/10.01.51.00005>

Accessories



VSL 8-6 PU MI-TR

Part no.:10.07.09.00003

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 45 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -35 ... 60 °C

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr