

Hose sleeve

ST G1-1/4-AG 32 MS-V

Part no.:10.08.03.00169

<https://www.schmalz.com/10.08.03.00169>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Accessories for Screw Unions > ST G1-1/4-AG 32 MS-V

Hose sleeve



Thread G1: G1-1/4"-M

Hose diameter (rec.) d: 32 mm


Material: Brass

Surface: nickel plated

Length L: 10.3 mm

Nominal diameter dn: 27.9 mm

Design Data



Attribute	Value
dn	27.90 mm
D	32 mm
G1	G1-1/4"-M
L	10.30 mm
L1	62 mm
LG1	15.90 mm
SW1	46 mm

Technical Data

Attribute	Value
Material	Brass
Weight	251 g

Accessories

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr

Hose sleeve

ST G1-1/4-AG 32 MS-V

Part no.:10.08.03.00169

<https://www.schmalz.com/10.08.03.00169>



VSL 41-32 PVC-DS KL-TR

Part no.:10.07.09.00008

External diameter D: 41 mm

Internal diameter d: 32 mm

Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 110 mm

Pressure range (operating pressure): -0.85 ... 4.00 bar

Operating temperature: -15 ... 65 °C

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr