

Dust filter

STF G1-1/4-IG N

Part no.:10.07.01.00008

<https://www.schmalz.com/10.07.01.00008>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Vacuum Filters > Vacuum Filters VF / STF / STF-D > STF G1-1/4-IG N

Dust filter




Connection: G1-1/4"-F

Shape: Steel housing

Nominal flow rate: 96 m³/h

Filter pore size: 3 µm

Design Data



Attribute	Value
B1	81 mm
D	136 mm
G1	G1-1/4"-F
G2	G1-1/4"-F
L	116 mm
L1	191 mm
L2	17 mm

Technical Data

Attribute	Value
Connection	G1-1/4"-F
Nominal flow rate	96 m ³ /h
Nominal flow rate	1600 l/min
Max. vacuum	-950 mbar
Filter pore size	3 µm
Weight	1 kg
Product family	VF

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8162403
schmalz@schmalz.co.kr

Dust filter

STF G1-1/4-IG N

Part no.:10.07.01.00008

<https://www.schmalz.com/10.07.01.00008>

Spare parts



FILT-EINS 3 98x70 PAP STF-1-1/4-IGN

Part no.:10.07.01.00018

Filter pore size: 3 µm

External diameter D: 98 mm

Length L: 70 mm

Filter material: Paper

Construction use: Dust filter STF

Size: 1-1/4-IGN



FILT-EINS 3 98x70 PAP STF-1-1/4-IGN

Part no.:10.07.01.00018

Filter pore size: 3 µm

External diameter D: 98 mm

Length L: 70 mm

Filter material: Paper

Construction use: Dust filter STF

Size: 1-1/4-IGN

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr