

Ball joint

KGL G1/4-IG G1/4-AG

Part no.:10.01.03.00110

<https://www.schmalz.com/10.01.03.00110>

Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Jointed Mountings > Ball Joints
KGL > KGL G1/4-IG G1/4-AG

Suction cup mounting with joint for adaptation to sloping surfaces




Thread G1: G1/4"-F

Thread G2: G1/4"-M

Height H: 37.5 mm

Design Data



Attribute	Value
dn	3.50 mm
H	37.50 mm
G1	G1/4"-F
G2	G1/4"-M
LG1	12 mm
LG2	10 mm
SW1	19 mm
W	15 °

Technical Data

Attribute	Value
Vertical load	1500 N
Weight	67 g
Product family	KGL

Spare parts

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr

Ball joint

KGL G1/4-IG G1/4-AG

Part no.:10.01.03.00110

<https://www.schmalz.com/10.01.03.00110>



DR G1/4 18/13.5x1.5 PA

Part no.:10.07.08.00021

for: G1/4

External diameter D: 18 mm

Internal diameter d: 13.5 mm

Material: Polyamide

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr