

Suction cup (round)

SAUG-SCGS 40 SI-HD-65 602 B

Part no.:10.01.30.01105

<https://www.schmalz.com/10.01.30.01105>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Flow Grippers > Suction Cups for Flow Grippers SCGS > SAUG-SCGS 40 SI-HD-65 602 B

Suction cup (round)




Size: 40

Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Suct. cups: Bell. suct. cup f. SCG(S)

Design Data



Attribute	Value
Dmax (N)	25 mm
Dmax(S)	42 mm
dn	27 mm
Ds	39.40 mm
G1	M20x1-F
H	29 mm
LG1	6.50 mm
Z (Stroke)	6.50 mm

Technical Data

Attribute	Value
Size	40
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65 Shore A
Weight	26 g
Product family	SAUG-SCGS

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Suction cup (round)

SAUG-SCGS 40 SI-HD-65 602 B

Part no.:10.01.30.01105

<https://www.schmalz.com/10.01.30.01105>

Spare parts



BCG 40 SI-HD-65 SC095

Part no.:10.01.06.04847

Size: 40

Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr