

Holder system

HTS-A3 D SGM 30/40 OP

Part no.:10.01.17.00582

<https://www.schmalz.com/10.01.17.00582>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Magnetic Grippers > Holder System
Magnetic Grippers SGM > HTS-A3 D SGM 30/40 OP

Holder system




Connection 1: Ball head 28.5 mm

Construction use: Magnetic gripper

Size: 30/40

Shape: Double block

Design Data



Attribute	Value
B	59 mm
B2	7.20 mm
d	4.50 mm
D	28.50 mm
H	9.40 mm
H1	48.30 mm
H2	5.50 mm
H3	27.10 mm
H4	35 mm
L	59 mm
X1	46 mm
Y1	21.20 mm

Technical Data

Attribute	Value
Size	30/40
Material	Aluminum
Weight	108.20 g

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8162403
schmalz@schmalz.co.kr

Holder system

HTS-A3 D SGM 30/40 OP

Part no.:10.01.17.00582

<https://www.schmalz.com/10.01.17.00582>

Accessories



HTR-UNI 2N X3

Part no.:10.01.03.00302

Suction cup connection: ball head 28.5 mm

Operating temperature: °C

Cross-beam connection: 2 T-slots

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr