

Mouting bracket (inst.)


BEF-WIN 72x25x77 SBPL/SCPL

Part no.:10.02.01.01705

<https://www.schmalz.com/10.02.01.01705>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Basic Ejectors > BEF-WIN 72x25x77 SBPL/SCPL

Mouting bracket (inst.)




Length L: 72 mm

Width B: 25 mm

Height H: 77 mm

Design Data



Attribute	Value
B	25 mm
B3	10 mm
d1	4.50 mm
d2	6.60 mm
H	77 mm
H2	13.50 mm
H3	6 mm
L	72 mm
X1	41 mm
X2	60 mm
X3	52 mm
Y1	60 mm
Y2	52.50 mm
Y3	21.50 mm
s	3 mm

Technical Data

Attribute	Value
Pressure range (operating pressure)	bar
Operating temperature	°C

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr



Mouting bracket (inst.)

BEF-WIN 72x25x77 SBPL/SCPL

Part no.:10.02.01.01705

<https://www.schmalz.com/10.02.01.01705>

Weight

110.90 g

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8624031
schmalz@schmalz.co.kr