

## Suction cup cover

SU 100

Part no.:10.01.01.12840

<https://www.schmalz.com/10.01.01.12840>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Accessories Vacuum Suction Cups > Suction Cup Covers SU > SU 100

### Cover for suction cup




Size: 100

Clamping range: 100.0 ... 115.0 mm

Temperature resistance: 80 °C

### Dati di costruzione



| Attributo | Valore |
|-----------|--------|
| d         | 5 mm   |
| D         | 111 mm |
| D2        | 50 mm  |

### Dati tecnici

| Attributo      | Valore             |
|----------------|--------------------|
| Size           | 100                |
| Clamping range | 100.0 ... 115.0 mm |
| Weight         | 2.20 g             |
| Product family | SU                 |

Note: In vertical applications with a suction plate or cup, the lateral force sinks by up to 70%. The vacuum generator must be able to provide 10% more suction power

### Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031  
schmalz@schmalz.co.kr