

Flat suction cup (oval)

SGO 24x8 NBR-ESD-55 N022

Part no.:10.01.05.00934

<https://www.schmalz.com/10.01.05.00934>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > SGO 24x8 NBR-ESD-55 N022


Flat suction cup (oval) for narrow or curved workpieces



Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
Bmax(S)	9 mm
Bs	7.60 mm
d	5.50 mm
d1	7 mm
dn	1.50 mm
Dk	11.50 mm
Lmax(S)	24.50 mm
Ls	23.60 mm
H	12 mm
H2	3 mm
H3	5.50 mm
Z (Stroke)	1 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	8 N
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55 Shore A
Weight	1 g
Product family	SGO

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr



Flat suction cup (oval)

SGO 24x8 NBR-ESD-55 N022

Part no.:10.01.05.00934

<https://www.schmalz.com/10.01.05.00934>

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr