

Flat suction cup (round)

SUF 35 NBR-55 SC050

Part no.:10.01.01.13950

<https://www.schmalz.com/10.01.01.13950>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SUF 35 NBR-55 SC050

Flat suction cup (round) f. process- safe handling of smooth or slightly rough surfaces




Size: 35

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d1	17.20 mm
d	11 mm
Dk	23.30 mm
Dmax(S)	39.20 mm
Ds	35 mm
H	14.90 mm
H2	6.80 mm
H3	9.30 mm
Z (Stroke)	3.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	46 N
Pull-off force	46 N
Volume	2.40 cm ³
Curve radius (min) (convex)	40 mm
Size	35
Nipple family	SC050
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Flat suction cup (round)

SUF 35 NBR-55 SC050

Part no.:10.01.01.13950

<https://www.schmalz.com/10.01.01.13950>

Weight	5.50 g
Product family	SUF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SC 050 G1/8-AG

Part no.:10.01.06.04250

Connection geometry: 050
Vacuum connection: G1/8"-M
Fitting length: 7.2 mm
Nominal diameter dn: 4.1 mm



SC 050 G1/8-IG

Part no.:10.01.06.04308

Connection geometry: 050
Vacuum connection: G1/8"-F
Fitting length: 14 mm
Nominal diameter dn: 6.1 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr