

## Flat suction cup (round)

SHF 70 NK-45 N041 MOS

Part no.:10.01.01.11686

<https://www.schmalz.com/10.01.01.11686>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SHF 70 NK-45 N041 MOS

### Flat suction cup (round) for highly dynamic handling of wood




Size: 70

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A

### Design Data



| Attribute  | Value    |
|------------|----------|
| d          | 7.50 mm  |
| d1         | 17 mm    |
| d2         | 36 mm    |
| Dk         | 17 mm    |
| Dmax(S)    | 74 mm    |
| Ds         | 70 mm    |
| H          | 22.20 mm |
| H2         | 12.80 mm |
| H3         | 14.30 mm |
| Z (Stroke) | 4 mm     |

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

### Technical Data

| Attribute                | Value                 |
|--------------------------|-----------------------|
| Size                     | 70                    |
| Nipple family            | N 041                 |
| Number of folds          | 0                     |
| Lateral force            | 145 N                 |
| Suction force (-600mbar) | 155 N                 |
| Suction cup material     | Natural Rubber NK     |
| Volume                   | 13.30 cm <sup>3</sup> |

### Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031  
schmalz@schmalz.co.kr

## Flat suction cup (round)

SHF 70 NK-45 N041 MOS

Part no.:10.01.01.11686

<https://www.schmalz.com/10.01.01.11686>

Curve radius (min) (convex) 95 mm

Weight 28.90 g

Product family SHF

### Accessories



#### SA-NIP N041 G1/4-AG DN440

Part no.:10.01.01.11772

Thread G1: G1/4"-M

Fitting length: 4 mm

Material: Aluminum



#### SA-NIP N041 G1/4-IG DN440

Part no.:10.01.01.11822

Thread G1: G1/4"-F

Fitting length: 15 mm

Material: Aluminum



#### SIEB 15x0.8 MS-A2 0.103/0.07

Part no.:10.07.01.00211

External diameter D: 15 mm

Length L: 0.8 mm

Material: Brass / Stainless steel

### Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031  
schmalz@schmalz.co.kr

## Flat suction cup (round)

SHF 70 NK-45 N041 MOS

Part no.:10.01.01.11686

<https://www.schmalz.com/10.01.01.11686>



### TVN G1/4-AG 8.4 N041

Part no.:10.05.10.00058

Thread G1: G1/4"-M

Spring stroke Z: 8.4 mm

Nipple: N 041

## Spare parts



### DR 46/36x5 S05 EPDM-15 KE

Part no.:10.01.06.01678

External diameter D: 46 mm

Internal diameter d: 36 mm

Height H: 5 mm

Material type: Foam S, Height 5 mm

Sealing material: EPDM

Material hardness [Shore A]: 15 Shore A

Add. function: Adhesive tape on one side

## Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031  
schmalz@schmalz.co.kr