

Flat suction cup (round) sensitive

SGN 10 NBR-55 M5-AG

Part no...:10.01.01.00198

<https://www.schmalz.com/10.01.01.00198>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Different Industries > Flat Suction Cups SGN > SGN 10 NBR-55 M5-AG

Flat suction cup (round), handling sensitive workpieces with uneven surfaces



Size: 10


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Connection: M5-AG

Design Data



Attribute	Value
Dmax(S)	11 mm
dn	2 mm
Ds	10 mm
G1	M5-M
H	16 mm
LG1	4.50 mm
SW1	8 mm
Z (Stroke)	2 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Number of folds	0
Size	10
Suction cup material	Nitrile rubber NBR
Suction force (-600mbar)	4 N
Material hardness [Shore A]	55 Shore A

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269 México | +52 442 209 52 26
schmalz@schmalz.com.mx

Flat suction cup (round) sensitive

SGN 10 NBR-55 M5-AG

Part no.:10.01.01.00198

<https://www.schmalz.com/10.01.01.00198>

Spare parts



SA-NIP N025 M5-AG DN200

Part no.:10.01.01.00318

Thread G1: M5-M

Fitting length: 3 mm

Material: Aluminum



SG 10 NBR-55 N025

Part no.:10.01.01.00194

Size: 10

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Height H: 13.5 mm

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | +52 442 209 52 26
schmalz@schmalz.com.mx