

Flat suction cup (round)

SUF 40 NBR-55 SC050

Part no...:10.01.01.13951

<https://www.schmalz.com/10.01.01.13951>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SUF 40 NBR-55 SC050

Flat suction cup (round) f. process- safe handling of smooth or slightly rough surfaces




Size: 40

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d1	17.20 mm
d	11 mm
Dk	24.80 mm
Dmax(S)	44 mm
Ds	40 mm
H	16 mm
H2	6.80 mm
H3	9.30 mm
Z (Stroke)	4 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	61 N
Pull-off force	61 N
Volume	3.80 cm ³
Curve radius (min) (convex)	50 mm
Size	40
Nipple family	SC050
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Weight	8.50 g

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269 México | +52 442 209 52 66
schmalz@schmalz.com.mx

Flat suction cup (round)

SUF 40 NBR-55 SC050

Part no.:10.01.01.13951

<https://www.schmalz.com/10.01.01.13951>

Product family

SUF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SC 050 G1/8-AG

Part no.:10.01.06.04250

Connection geometry: 050

Vacuum connection: G1/8"-M

Fitting length: 7.2 mm

Nominal diameter dn: 4.1 mm



SC 050 G1/8-IG

Part no.:10.01.06.04308

Connection geometry: 050

Vacuum connection: G1/8"-F

Fitting length: 14 mm

Nominal diameter dn: 6.1 mm

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx