

Flat suction cup (round)

SUF 25 SI-55 SC040

Part no...:10.01.01.13970

<https://www.schmalz.com/10.01.01.13970>


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SUF 25 SI-55 SC040

Flat suction cup (round) f. process- safe handling of smooth or slightly rough surfaces



Size: 25
Suction cup material: Silicone SI
Material characteristics: FDA-compatible
Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d1	10.50 mm
d	7 mm
Dk	15.50 mm
Dmax(S)	28.20 mm
Ds	25 mm
H	11.20 mm
H2	4.80 mm
H3	6.70 mm
Z (Stroke)	2.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	23 N
Pull-off force	23 N
Volume	0.90 cm ³
Curve radius (min) (convex)	25 mm
Size	25
Nipple family	SC040
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A
Weight	2.50 g

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269 México | + 52 442 209 52 26
schmalz@schmalz.com.mx

Flat suction cup (round)

SUF 25 SI-55 SC040

Part no.:10.01.01.13970

<https://www.schmalz.com/10.01.01.13970>

Product family

SUF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SC 040 G1/8-AG

Part no.:10.01.06.02490

Connection geometry: 040

Connection: G1/8"-M

Length L1: 20.2 mm

Fitting length: 6 mm

Nominal diameter dn: 4.1 mm



SC 040 G1/8-IG

Part no.:10.01.06.02482

Connection geometry: 040

Connection: G1/8"-F

Length L1: 20.7 mm

Fitting length: 14 mm

Nominal diameter dn: 4.1 mm

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 5211
schmalz@schmalz.com.mx