

Friction plate


ISRPL 86x86x8.7 NBR-55 d5

Part no...:10.01.15.00402

<https://www.schmalz.com/10.01.15.00402>


Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Accessories and Spare Parts > ISRPL 86x86x8.7 NBR-55 d5

Friction plate



Width B: 86 mm
Internal diameter d: 5 mm
Height H: 8.7 mm
Length L: 86 mm
Suction cup material: Nitrile rubber NBR-55
Type: CUP 100

Design Data



Attribute	Value
B	86 mm
d	5 mm
H	8.70 mm
L	86 mm