

Vacuum Area Gripper


FMP-S-SW90 1036 5R36 SPB2-20P F G60

Part no...:10.01.38.03512

<https://www.schmalz.com/10.01.38.03512>


Home > Vacuum Technology for Automation > Vacuum Components > Area Gripping Systems and End Effectors > Vacuum Area Gripping System
FXP/FMP > Area Gripping Systems FMP > FMP-S-SW90 1036 5R36 SPB2-20P F G60

Vacuum area gripping system for external vacuum generator, with flow resistors



Length L: 1,036 mm
Width B: 130 mm
Arrangement: 5R36
Add. function: Filter
construction shape fittings: Straight
External diameter D: 60 mm
Add. function: 1x control valve vacuum/blow-off
Max. air consumption blow off: 800 l/min
Construction shape vacuum switch: PNP switching
Weight: 6.1 kg
Product family: FMP

Design Data



Attribute	Value
B	130 mm
B3	21.60 mm
D	60 mm
H	82.70 mm
H1	128.20 mm
H2	33 mm
H3	7.70 mm
H4	5.50 mm
H5	46 mm
L	1036 mm
L2	996 mm
L3	77 mm
Y1	90 mm
Valve type	SW

Note: Vacuum hose with internal diameter equal to dimension D required. See Technical Data -> Shape

Technical Data

Attribute	Value
Arrangement	5R36

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | 52 442 209 5200
schmalz@schmalz.com.mx

Vacuum Area Gripper

FMP-S-SW90 1036 5R36 SPB2-20P F G60

Part no.:10.01.38.03512

<https://www.schmalz.com/10.01.38.03512>

Number of suction cells	137
Suction force at -250 mbar	350 N
Add. function	Filter
Add. function	Filter
Add. function	1x control valve vacuum/blow-off
Weight	6.10 kg
Sealing element	Suction Cups
Evacuation rate for pu = -0,25 bar	750 l/min
Product family	FMP

For compressed air with 5.5 bar input pressure At -0.25 bar and with the gripper fully covered by a workpiece typical for the application (wooden board with structured surface) The external vacuum generator used must supply at least the specified suction flow (at the vacuum connection piece of the FMP) at -0.25 bar but max. 135 % of the specified suction flow

Accessories



ABDK-PROF-10x7x1450-KU-SW-FXP-FMP

Part no.:26.07.03.00002

Length L: 1,450 mm


Width B: 10 mm

Height H: 7 mm

Material: Plastics

Measuring range: bar

Construction use: Vacuum area gripping system FXP-FMP



FLAN-PL 120x85x10 ST FLGR

Part no.:10.01.10.05701

Length L: 120 mm

Width B: 85 mm

Height H: 10 mm

Material: Steel

Construction use: Vacuum area gripping system

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | 52 442 209 52 269 216 000 | schmalz@schmalz.com.mx

Vacuum Area Gripper

FMP-S-SW90 1036 5R36 SPB2-20P F G60

Part no...:10.01.38.03512

<https://www.schmalz.com/10.01.38.03512>



FLK G1/2-IG G1/2-AG

Part no...:10.01.03.00175

Thread G1: G1/2"-F

Thread G2: G1/2"-M

Operating temperature: 0 ... 70 °C



FST-FLEX 25 HD1 G1/2-AG G3/8-IG

Part no...:10.01.10.05697

Spring stroke Z: 25 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section



FST-FLEX 25 HD2 G1/2-AG G3/8-IG

Part no...:10.01.10.05695

Spring stroke Z: 25 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | 52 442 209 52 269 91600 | schmalz@schmalz.com.mx

Vacuum Area Gripper

FMP-S-SW90 1036 5R36 SPB2-20P F G60

Part no...:10.01.38.03512

<https://www.schmalz.com/10.01.38.03512>



FST-FLEX 50 HD1 G1/2-AG G3/8-IG

Part no...:10.01.10.05687

Spring stroke Z: 50 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section



FST-FLEX 50 HD2 G1/2-AG G3/8-IG

Part no...:10.01.10.05168

Spring stroke Z: 50 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section



FST-FLEX 75 HD1 G1/2-AG G3/8-IG

Part no...:10.01.10.05698

Spring stroke Z: 75 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | 52 442 209 52 269 16 000 | schmalz@schmalz.com.mx

Vacuum Area Gripper

FMP-S-SW90 1036 5R36 SPB2-20P F G60

Part no...:10.01.38.03512

<https://www.schmalz.com/10.01.38.03512>



FST-FLEX 75 HD2 G1/2-AG G3/8-IG

Part no...:10.01.10.05696

Spring stroke Z: 75 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section



FST-STARR 25 HD1 G1/2-AG G3/8-IG

Part no...:10.01.10.05810

Spring stroke Z: 25 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section



FST-STARR 25 HD2 G1/2-AG G3/8-IG

Part no...:10.01.10.05806

Spring stroke Z: 25 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | 52 442 209 52 269 51600 | schmalz@schmalz.com.mx

Vacuum Area Gripper

FMP-S-SW90 1036 5R36 SPB2-20P F G60

Part no...:10.01.38.03512

<https://www.schmalz.com/10.01.38.03512>



FST-STARR 50 HD1 G1/2-AG G3/8-IG

Part no...:10.01.10.05809

Spring stroke Z: 50 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section



FST-STARR 50 HD2 G1/2-AG G3/8-IG

Part no...:10.01.10.05805

Spring stroke Z: 50 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section



FST-STARR 75 HD1 G1/2-AG G3/8-IG

Part no...:10.01.10.05808

Spring stroke Z: 75 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269 México | 52 442 209 52 269 16 000 | schmalz@schmalz.com.mx

Vacuum Area Gripper

FMP-S-SW90 1036 5R36 SPB2-20P F G60

Part no...:10.01.38.03512

<https://www.schmalz.com/10.01.38.03512>



FST-STARR 75 HD2 G1/2-AG G3/8-IG

Part no...:10.01.10.05803

Spring stroke Z: 75 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section



MOD-FLAN 120x120 FXP-FMP

Part no...:10.01.21.00244

Length L: 120 mm

Width B: 120 mm

Height H: 60 mm

Weight: 1.1 kg

Measuring range: bar

Construction use: Vacuum area gripping system FXP-FMP



SET fuer-Sensor(FXP/FMP)

Part no...:10.01.38.01194

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | 1 52 442 209 52 269 1600 | schmalz@schmalz.com.mx

Vacuum Area Gripper

FMP-S-SW90 1036 5R36 SPB2-20P F G60

Part no...:10.01.38.03512

<https://www.schmalz.com/10.01.38.03512>



SET FXC-FMC

Part no...:10.01.21.01291

Length L: 119 mm

Width B: 119 mm

Height H: 9.6 mm

Measuring range: bar

Construction use: Vacuum area gripping system FXC-FMC



SET FXP-FMP

Part no...:10.01.21.02407

Length L: 232 mm

Width B: 119 mm

Height H: 119 mm

Measuring range: bar

Construction use: Vacuum area gripping system FXP-FMP



SET FXP-FMP 4NUTSTEIN

Part no...:10.01.21.00243

contains: 4 slot nuts

Measuring range: bar

Construction use: Vacuum area gripping system FXP-FMP

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | +52 442 209 52 26
schmalz@schmalz.com.mx

Vacuum Area Gripper

FMP-S-SW90 1036 5R36 SPB2-20P F G60

Part no...:10.01.38.03512

<https://www.schmalz.com/10.01.38.03512>



STF 60 P 4.5 SSD

Part no...:10.07.01.00259

Connection: Ø60mm

Shape: Piclon housing

Nominal flow rate: 270 m³/h

Filter pore size: 3 µm

Additional function: Hose clamps SSD



VAM 40 V U BAR

Part no...:10.07.02.00046

External diameter D: 40 mm

Measuring range: -1,00 ... 0,00 bar



VENT-EINH 8/6 NC 24V-DC

Part no...:10.01.21.02405

Construction use: Vacuum area gripping system FXP-FMP

Connection: Hose 8/6

Control valve: Normally closed

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | 52 442 209 52 266 916 000 | schmalz@schmalz.com.mx

Vacuum Area Gripper

FMP-S-SW90 1036 5R36 SPB2-20P F G60

Part no...:10.01.38.03512

<https://www.schmalz.com/10.01.38.03512>



VSL 71-60 PU-DS-AS TR

Part no...:10.07.09.00034

External diameter D: 71 mm

Internal diameter d: 60 mm


Length max.: 20 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 40 mm

Pressure range (operating pressure): -0.69 ... 2.09 bar

Operating temperature: -40 ... 90 °C



VS-MONT 50x15.8x25 VS

Part no...:10.06.02.00343

Length L: 50 mm

Width B: 15.8 mm

Height H: 25 mm

Measuring range: bar

Construction use: Vacuum switch



VS-MONT 76.5x19 VSi FXP-FMP

Part no...:10.01.38.02485

Length L: 76.5 mm

Width B: 19 mm

Add. function: Vacuum and pressure switch VSi

Measuring range: bar

Add. function: Vacuum and pressure switch

Construction use: Vacuum area gripping system FXP-FMP

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | +52 442 209 52 26
schmalz@schmalz.com.mx

Vacuum Area Gripper

FMP-S-SW90 1036 5R36 SPB2-20P F G60

Part no...:10.01.38.03512

<https://www.schmalz.com/10.01.38.03512>



VTR-SL 3x RST60

Part no...:10.01.10.02779

Length L: 439 mm

Width B: 100 mm

Height H: 156 mm

Connection: Tube end Ø60



ASK B-M12-5 5000 K-5P

Part no...:21.04.05.00080

Electrical connection: Fem connect M12, 5 pol

Cable length: 5,000 mm

Material hose: PUR cable



VSL 8-6 PU MI-TR

Part no...:10.07.09.00003

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 45 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -35 ... 60 °C

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | +52 442 209 52 26
schmalz@schmalz.com.mx

Vacuum Area Gripper

FMP-S-SW90 1036 5R36 SPB2-20P F G60

Part no...:10.01.38.03512

<https://www.schmalz.com/10.01.38.03512>



FLAN-PL 120x120x10 FXC-FMC

Part no...:10.01.21.00313

Length L: 120 mm

Width B: 120 mm

Height H: 10 mm

Measuring range: bar

Construction use: Vacuum area gripping system FXC-FMC



FLK G1/2-IG G1/2-AG V

Part no...:10.01.03.00207

Thread G1: G1/2"-F

Thread G2: G1/2"-M

Operating temperature: 0 ... 70 °C

Shape mounting elements: Reinforced

Spare parts



VENT-BGR FMP-S-50

Part no...:10.01.38.03682

Construction use: Vacuum area gripping system FMP-S

contains: Way-valve pneumatic

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | +52 442 209 52 26
schmalz@schmalz.com.mx

Vacuum Area Gripper

FMP-S-SW90 1036 5R36 SPB2-20P F G60

Part no...:10.01.38.03512

<https://www.schmalz.com/10.01.38.03512>



SPB2 20 SI-40 P F

Part no...:10.01.38.00465

Add. function: Filter

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | +52 442 209 52 26
schmalz@schmalz.com.mx