

Ball joint

KGL G1/4-IG M10x1.25-AG

Part no...:10.01.03.00137

<https://www.schmalz.com/10.01.03.00137>

Home > Ball Joints KGL > KGL G1/4-IG M10x1.25-AG

Suction cup mounting with joint for adaptation to sloping surfaces




Thread G1: G1/4"-F

Thread G2: M10x1.25-M

Height H: 37.5 mm

Design Data



Attribute	Value
dn	3.50 mm
H	37.50 mm
G1	G1/4"-F
G2	M10x1.25-M
LG1	12 mm
LG2	10 mm
SW1	19 mm
W	15 °

Technical Data

Attribute	Value
Vertical load	1500 N
Weight	67 g
Product family	KGL

Spare parts

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx

Ball joint

KGL G1/4-IG M10x1.25-AG

Part no...:10.01.03.00137

<https://www.schmalz.com/10.01.03.00137>



DR G1/4 18/13.5x1.5 PA

Part no...:10.07.08.00021

for: G1/4

External diameter D: 18 mm

Internal diameter d: 13.5 mm

Material: Polyamide

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx