

Flange plate (round)

FLAN-PL 55x9.5-JP1

Part no...:10.01.30.00194

<https://www.schmalz.com/10.01.30.00194>



Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Thin Glass Grippers > Accessories STGG > FLAN-PL 55x9.5-JP1

Flange plate (round)




External diameter D: 55 mm

Length L: 9.5 mm

Size: JP1

Thread G1: G3/8"-F

Design Data



Attribute	Value
d1	4.50 mm
d2	5.50 mm
d3	6.60 mm
d4	4.50 mm
D	55 mm
Dmk	25 mm
D mk1	31.50 mm
D mk2	40 mm
D mk3	46 mm
D mk4	48 mm
G1	G3/8"-F
G2	M4-F
L	9.50 mm
L3	6.30 mm

Technical Data

Attribute	Value
Pressure range (operating pressure)	bar
Weight	27 g

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx



Flange plate (round)

FLAN-PL 55x9.5-JP1

Part no...:10.01.30.00194

<https://www.schmalz.com/10.01.30.00194>

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx