

Controller

STEU 24V-DC OFG-C

Part no...:10.01.51.00006

<https://www.schmalz.com/10.01.51.00006>




Home > Vacuum Technology for Automation > Vacuum Components > Area Gripping Systems and End Effectors > Finger Grippers > STEU 24V-DC OFG-C

Controller



Voltage DC: 24V - DC
Construction use: Finger gripper controlled
Operating temperature: 0 ... 50 °C
Pressure range (operating pressure): 6.0 ... 8.0 bar
Hose type: Hose D = 8 d = 6
Weight: 2,500 g

Design Data



Attribute	Value
B	162.50 mm
d	9 mm
d1	9 mm
H	90 mm
L	275 mm
X1	260 mm
Y1	122 mm

Technical Data

Attribute	Value
Voltage DC	24V - DC
Hose type	Hose D = 8 d = 6
Pressure range (operating pressure)	6.0 ... 8.0 bar
Operating temperature	0 ... 50 °C
Weight	2500 g

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx

Controller

STEU 24V-DC OFG-C

Part no.:10.01.51.00006

<https://www.schmalz.com/10.01.51.00006>

Accessories



VSL 8-6 PU MI-TR

Part no.:10.07.09.00003

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 45 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -35 ... 60 °C

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx