

Vacuum pump

EVE-OG 63 AC3 AQUA IE2

Part no.:10.03.02.00076

<https://www.schmalz.com/10.03.02.00076>

Home > Vacuum Clamping Technology > Vacuum Generators > Vacuum Generators for CNC Machining Centers > EVE-OG 63 AC3 AQUA IE2

Oil-lubricated pump for maximum vacuum levels, requires little maintenance



Length L: 626 mm

Current type: three-phase current

Voltage at 50Hz: 190-208V/380-415V AC3


Voltage at 60Hz: 220-230V/440-480V AC3

Rated power 50 Hz: 2 kW

Rated power 60 Hz: 2.4 kW

Suction rate (50 Hz): 63 m³/h

Design Data



Attribute	Value
B	407 mm
G3	G1-1/4"-F
G5	M8-F
H	290 mm
L	626 mm

Technical Data

Attribute	Value
Max. vacuum	-980 mbar
Rated power 50 Hz	2 kW
Rated power 60 Hz	2.40 kW
Suction rate (50 Hz)	63 m³/h
Suction rate	63 m³/h
Protection type IP	IP 55
Voltage at 50Hz	190-208V/380-415V AC3
Voltage at 60Hz	220-230V/440-480V AC3
Current type	three-phase current

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 5211
schmalz@schmalz.com.mx

Vacuum pump

EVE-OG 63 AC3 AQUA IE2

Part no...:10.03.02.00076

<https://www.schmalz.com/10.03.02.00076>

Type

AQUA

Accessories



OEL EVE-OG 1L ANDEROL 555

Part no...:27.02.01.00055

Construction use: Pump EVE-OG

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76600 México | + 52 442 209 52 26
schmalz@schmalz.com.mx