

Solenoid valve pressure

EMV 1.5 24V-DC 3/2 NC K-2P

Part no.:10.05.01.00288

<https://www.schmalz.com/10.05.01.00288>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Thin Glass Grippers > Accessories STGG > EMV 1.5 24V-DC 3/2 NC K-2P

Solenoid valve EMV for direct control of compressed air



Nominal size: 1.5 mm

Voltage DC: 24V - DC

Function: 3/2-way valve


Control valve: Normally closed

Connecting thread: M5-M

Pressure range (operating pressure): 3.5 ... 7.0 bar

Interface electrical connection: Cable, 2 pol

Design Data



Attribute	Value
B1	26.60 mm
B2	8.10 mm
d	4 mm
G1	M5-M
G2	M5-F
L	43.10 mm
L1	46.50 mm

Technical Data

Attribute	Value
Nominal size	1.50 mm
Control valve	Normally closed
Nominal flow rate	45 l/min
Nominal flow rate	2.70 m³/h
Voltage DC	24V - DC
Weight	0.07 kg
Product family	EMV

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | +52 442 209 52 26
schmalz@schmalz.com.mx



Solenoid valve pressure

EMV 1.5 24V-DC 3/2 NC K-2P

Part no...:10.05.01.00288

<https://www.schmalz.com/10.05.01.00288>

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 5200
schmalz@schmalz.com.mx